

Data Sheet | Item Number: 211-125

Nozzles; Length: 23 mm; only for use with 211-110/-111/-120/-121; halogen-free;
Cable outer diameter: 5.5 ... 10.0 mm; black

<https://www.wago.com/211-125>



Color: ■ black

Similar to illustration

Technical data		
Suitable		for wire diameter 5.5 ... 10 mm or 10 ... 25 mm
Delivery form		Component
Properties		23 mm long; for one marker
Printing device		TP 298+

Physical data		
Length		23 mm

Mechanical data		
Mounting type		Sliding on conductor

Material data		
Color		black
Material		Polyurethane
Adhesive information		without adhesive
Halogen-free		Yes
Weight		0.6 g
Fire load		0 MJ

Environmental requirements		
Ambient temperature (storage)		+10 ... +25 °C
Ambient temperature (operation)		-40 ... +100 °C
Relative humidity		40 ... 60 %



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	1000 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454486136
Customs tariff number	39269097900

Product Classification	
UNSPSC	39121722
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 9.0	EC001530
ETIM 8.0	EC001530
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-125

↓

1 Compatible Products
1.1 Required Accessories
1.1.1 Marking
1.1.1.1 Marker



Item No.: 211-121
Marker; for TP printers; for use in nozzles;
Length: 23 mm; white