
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	"C"	"HC"	"TC"	"L"
HC1.5**6	1.89 ± .01 [48.0 ± 0.25]	.44 ± .02 [11.2 ± 0.5]	.06 ± .01 [1.5 ± 0.25]	72.00 ± .18 [1828.8 ± 4.6]
HC2**6	2.29 ± .01 [58.2 ± 0.25]			
HC3**6	3.39 ± .01 [86.1 ± 0.25]			
HC4**6	4.39 ± .01 [111.5 ± 0.25]			
HC2**2	2.29 ± .01 [58.2 ± 0.25]			78.74 ± .18 [2000.0 ± 4.6]



NOTES:
1. SEE CURRENT CATALOG FOR PART NUMBER DESIGNATIONS FOR TYPE, COLOR, AND LENGTH.
2. DIMENSIONS IN PARENTHESES ARE METRIC.
3. COVER TYPE "HC" TO BE USED WITH TYPE "H","HN"&"HS" DUCT. (SEE DWG # 38258-04)

PART NO. SYSTEM
CHANNEL EXAMPLE
H C 2 LG 6
TYPE
COVER
WIDTH
COLOR
LENGTH

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	03-05-13	JBN	RTFI	RTFI	I. UPDATED DRAWING BORDER & TITLE BLOCK	38258-05

TITLE
TYPE "HC" WIRING DUCT COVER
CUSTOMER DRAWING

ITEM REVISION NAME: D38258BD/01
DATASET FILE NAME: D38258BD_DC/01D

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ±
.XX ± .01 [.25] ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: SEE NOTES ABOVE

DRAWING NUMBER: 38258-05

DRAWN BY	DATE	CHK	SCALE	SIZE
JCST	11-29-01	JKG	NONE	A

SHT 1 OF 1

D10100DA/15

Downloaded from Arrow.com.