



Quality Products. Service Excellence.

## C4 Doors C4DF Series

Exclusively for use with the C4 Cabinet Series



### Features

- Constructed in 16-gauge steel.
- Easily installs into **C4 Series** cabinets using integrated spring pin at top and bottom of the door.
- Hinged on left, swings from right to left.
  - Need hinging on right? Order the **C4RHINGE**.
- Includes formed plastic handle, quarter-turn lock and hinges to mount on the cabinet.
- Available in Solid, Louvered, Perforated, **acrylic window** options.
- Finished in textured RAL9005 black powder paint coat.
  - Complies with the Greenguard guidelines for indoor air quality
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.

### Accessories

- Cabinet Door Replacement Lock
- Split Door Retrofit Kit

### Flush with Frame with Locking Quarter Turn

| Part No.     | Part No.     | Part No.     | Part No.            | Use with Cabinet |       |
|--------------|--------------|--------------|---------------------|------------------|-------|
| Solid        | Window       | Vented       | Vented Split (Barn) | Rack Units       | Width |
| C4DF2442SBK1 | C4DF2442PBK1 | C4DF2442VBK1 | C4BD2442VBK1        | 24U              | 24.00 |
| C4DF2473SBK1 | C4DF2473PBK1 | C4DF2473VBK1 | C4BD2473VBK1        | 42U              | 24.00 |
| C4DF2477SBK1 | C4DF2477PBK1 | C4DF2477VBK1 | C4BD2477VBK1        | 44U              | 24.00 |
| C4DF3077SBK1 | C4DF3077PBK1 | C4DF3077VBK1 | C4BD3077VBK1        | 44U              | 30.00 |

\*Perforated doors for both front and back of the cabinet are suggested for most server applications.

### Surface Door with Locking Swinghandle

| Part No.    | Part No.    | Part No.    | Part No.            | Use with Cabinet |       |
|-------------|-------------|-------------|---------------------|------------------|-------|
| Solid       | Window      | Vented      | Vented Split (Barn) | Rack Units       | Width |
| C4D2442SBK1 | C4D2442WBK1 | C4D2442VBK1 | C4D2442BBK1         | 24U              | 24.00 |
| C4D2473SBK1 | C4D2473WBK1 | C4D2473VBK1 | C4D2473BBK1         | 42U              | 24.00 |
| C4D2477SBK1 | C4D2477WBK1 | C4D2477VBK1 | C4D2477BBK1         | 44U              | 24.00 |
| C4D3077SBK1 | C4D3077WBK1 | C4D3077VBK1 | C4D3077BBK1         | 44U              | 30.00 |

Data subject to change without notice

