



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)  
SOC CONN CVR ASSY,12 P,AMPSEAL 16,90 DEG  
[AMP](#) | [AMPSEAL 16](#)

2302495-2  
TE Internal Number: 2302495-2

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Connector System** Wire-to-Wire
- Accessory Type** Backshell Kit
- Cable Exit Angle** 90 (Right Angle)
- Sealable** No
- Strain Relief** With

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

**BACKSHELL AND ELBOW KIT, 12 POSN PLUG ASSY, AMPSEAL 16**

PDF

**English**

CAD Files

**3D PDF**

PDF

**3D**

**Customer View Model**

2D\_DXF.ZIP

English

Customer View Model

3D\_IGS.ZIP

English

Customer View Model

3D\_STP.ZIP

English

Product Specifications

Product Specification

108-151043

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

INSTRUCTION SHEET, AMPSEAL 16 BACKSHELLS, VERTICAL AND RIGHT ANGLE

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire

Accessory Type Backshell Kit

Sealable No

Strain Relief With

Configuration Features

Number of Positions 12

Body Features

Cable Exit Angle 90 (Right Angle)

Color Black

Material PA

Usage Conditions

Operating Temperature Range -40 – 125 °C [ -40 – 257 °F ]

Operating Temperature (Max) 125 °C [ 257 °F ]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

**Packaging Method** Bag/Box

Other

**Serviceable** Yes

Statement of Compliance

**Statement of Compliance**

PDF