

# Eaton BSPMA3480WYGR

Catalog Number: BSPMA3480WYGR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, 277/480 V, Surge arrester, Thermoplastic, UL94V2, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

## General specifications



### Product Name

Eaton Bussmann series BSPM series  
surge arrester

### Catalog Number

BSPMA3480WYGR

### UPC

051712709095

### Product Length/Depth

2.13 in

### Product Height

3.54 in

### Product Width

2.56 in

### Product Weight

0.73 lb

### Warranty

Five year limited warranty

### Compliances

Contact factory  
RoHS Compliant

### Certifications

UL 94V0  
UL Listed

## Product specifications

### Special features

Technology type MOV

### Material

Thermoplastic

### Enclosure

Thermoplastic, UL94V2

### Surge current

200 kA

### Mounting Method

35 mm DIN rail

### Nominal Discharge Current

20 kA

### Short-circuit rating

200 kA

### Type

Surge arrestor

### Operating voltage

550

### Indicator type

Remote contact

### Frequency rating

50/60 Hz

### Operating temperature

-35 to 85 °C

### Voltage rating

277/480 V

### Application

Surge Protection

### Degree of protection

IP20

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

BSPMA3480WYGR-277/480 Wye, 3P

### Specifications and datasheets

Eaton Specification Sheet - BSPMA3480WYGR



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)