



Part Number : 1300940397

Product Description : Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1197.48kg (2640 lbs)



Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35291

Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single "U" Eye, Split Rod, Single Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1197.48kg (2640 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835291

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	1197.48kg (2640 lbs)
Bale Length	0.356m (14.00")
Body Style	Straight
Cable Diameter	44.45-50.55mm (1.750-1.990")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.508m (20.00")
Net Weight	350.985/g
Number of Holes	N/A
O-Ring	N/A

Thread Size	N/A
-------------	-----

This document was generated on Sep 14, 2025