

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			A	RELEASED PER ECR 09-017675	11AUG09	JR

AMP WIRE RANGE	 E13288 Listed
3/0 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE


- 1

STAMP AMP 3/0W* APPROX AS SHOWN
- 2


STAMP 150 APPROX AS SHOWN
- 3

TONGUE MATERIAL THK: 2.31±0.08[.091±.003]
- 4

PREPRODUCTION – FASR REQUIRED



CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 76.3-96.3mm²[150,000-190,000] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 02JUL09	 Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK R LONDON 02JUL09			
		APVD R LONDON 02JUL09	NAME TERMINAL, RING TONGUE, SOLISTRAND™		
		PRODUCT SPEC	—		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	—		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT	—	SIZE A2	CAGE CODE 00779
MATERIAL COPPER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM-545	DRAWING NO C=1958311		
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV A

7.75 [.305]	4	1958311-3
12.75 [.502]	4	1958311-2
10.75 [.423]	4	1958311-1
"A"		Part Number