

SPECIFICATIONS


| PARAMETERS              | VALUES          | UNITS         |
|-------------------------|-----------------|---------------|
| RATED VOLTAGE           | 12              | Vdc           |
| OPERATING VOLTAGE RANGE | 4 ~ 28          | Vdc           |
| RATED CURRENT (MAX)     | 6               | mA            |
| MINIMUM SPL @ 10 CM     | 88              | dBA           |
| RESONANT FREQUENCY      | 2,900 ± 500     | Hz            |
| TONE OR PULSE RATE      | SLOW PULSE      | 1.2 pulse/sec |
| OPERATING TEMPERATURE   | -20 ~ +60       | °C            |
| STORAGE TEMPERATURE     | -30 ~ +70       | °C            |
| HOUSING MATERIAL        | ABS             | -             |
| TERMINAL MATERIAL       | Ni PLATED BRASS | -             |
| WEIGHT                  | 43              | grams         |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.


REVISION HISTORY

| LTR | DESCRIPTION                             | DATE      | APPROVED |
|-----|-----------------------------------------|-----------|----------|
| -   | RELEASED FROM ENGINEERING               | 2/14/2006 |          |
| A   | REVISED PULSE RATE UNITS                | 4/2/2008  | B.R.     |
| B   | REVISED TO INVETOR 3-D DRAWING TEMPLATE | 4/10/2008 | B.R.     |
| C   | REVISED MOUNTING RING OUTER DIMENSIONS  | 2/25/2020 | M.V.     |



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

|                                                                                                                  |                |                                                                                                                        |           |            |                  |              |                |            |
|------------------------------------------------------------------------------------------------------------------|----------------|------------------------------------------------------------------------------------------------------------------------|-----------|------------|------------------|--------------|----------------|------------|
| UNLESS OTHERWISE SPECIFIED:<br><br>DIMENSIONS ARE IN MILLIMETERS,<br><br>TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE<br><br>A3 | Designed by                                                                                                            | Date      | Checked by | Date             | Approved by  | Date           | Drawn Date |
|                                                                                                                  |                | J.A.F.                                                                                                                 | 2/14/2006 | E.P.       | 2/14/2006        | B.R.         | 2/14/2006      | 4/10/2008  |
|                                                                                                                  |                |  <b>pui</b><br><b>audio</b> ™ inc |           |            | AI-4329-P-SP28-R |              |                |            |
|                                                                                                                  | Indicator      |                                                                                                                        |           |            |                  | Edition<br>- | Sheet<br>1 / 1 |            |
| AI-4329-P-SP28-R.idw                                                                                             |                |                                                                                                                        |           |            |                  |              |                |            |

