



CRIMP RINGS & SPADES



TE CONNECTIVITY (TE)

RING 16-12 10 018 NPST

[Open Barrel Rings & Spades](#) | [Open Barrel Rings & Spades](#)

640253-4

TE Internal Number: 640253-4

Always EU RoHS/ELV Compliant

Terminal Shape **Ring Tongue**

Stud Diameter **5 mm [.197 in]**

Heavy Duty **No**

Barrel Type **Open Barrel**

Plating Material **Nickel**

✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

Product Drawings

[Ring](#)

PDF
English

CAD Files

[3D PDF](#)

PDF
3D

[Customer View Model](#)

2D_DXF.ZIP
English

[Customer View Model](#)

3D_IGS.ZIP
English

[Customer View Model](#)

3D_STP.ZIP
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Barrel Type

Open Barrel

Wire/Cable Type

Regular Wire

Insulated

No

Insulated Wire Support

Yes

Body Features

Plating Material

Nickel

Contact Features

Terminal Shape

Ring Tongue

Dimensions

Stud Diameter

5 mm [.197 in]

Operation/Application

Heavy Duty

No

Packaging Features

Packaging Method

Reel

Packaging Quantity

8000

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)