Johanson Part Number 0900FM15K0039001E

Johanson Part Number: 0900FM15K0039001E	Johanson Company: JTI
Legacy P/N: 0900FM15K0039E	Size for Capacitors (EIA): None
Description: Matched Filters, 805, TX: 862-928, RX: 862-928MHz, 2W, 1.4dB, Ag/Pt (RoHS), Miniature Impedance-matched Filter for Semtech SX1261, SX1262, LLCC68 for 868MHz and 915MHz Operatio, 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.035
Schedule B: 8534.00.00.85	Thickness (Min): 0.027
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.018
RoHS Compliance: Yes, RoHS 10/10	Standard Item: No
REACH: Yes	Lead Time Typical (Weeks)*: 17
Country of Origin: TW	Length (Min): 0.073
Product Family: Integrated Passive Components	Length (Max): 0.085
Product Subfamily: Matched Filters	Width (Min):0.045
Capacitance Value: None	Width (Max): 0.053
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): +5°C to +35°C with RH 45% to 75%
Product Release Date: Feb. 22, 2022	Storage Temp Range (None Operating): -65°C to +125°C
Harmonization: 8534.00.00.85	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: https://www.johansontechnology.com/datasheets/0900FM15D0039/0900FM15D0039.pdf

Printed from: https://www.johansontechnology.com/part/0900FM15K0039001E/

Downloaded from Arrow.com.