




PRODUCT NUMBER

PITCH

KFxx10x000J0G

3.50 mm

RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item③Female contact: PhBz(CuSn), Tin plated
- Item④Terminal Cover: Thermoplastic (UL94V-0)
- Item⑤Terminal housing: Thermoplastic (UL94V-0)
- Item⑥Terminal housing (B type):Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 8A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C

Dimension

Dim A	N×3.5+1.50
Dim B	N×3.5
Dim C	(N-1)×3.5

N=Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-13p	±0.20
14p-18p	±0.30
19p-24p	±0.35

PART NO.: KF xx 10 x 0 00J0 G

End stackable	0	Color	Black (RAL9005)	RoHS compliant	(lead<4%)
No. of poles	2		Red (RAL3001/D)	In copper Alloy	
02 2 poles	3		Orange(RAL2011/P)		
03 3 poles	4		Yellow(RAL1018/A)		
...	...		Green(RAL6018/T)		
24 24 poles	5		Blue (RAL5015/A)		
	6		Grey(RAL7035/D)		
	9		White(RAL1102)		
	C		Green(RAL6018/U)		

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK			
					angles		title			
					0.015		TERMINAL BLOCK			
					X*±1°		PCB CONNECTOR,BOARD TO BOARD			
					dr	EVIN ZHONG	050614	dwg no		sheet 1 of 1
					enr	EVIN ZHONG	050614	KFxx10x000J0G		size
					chr	HANKE FENG	050614			A4
					appd	SHI JUN	050614	type		CUSTOMER Drawing
sheet index	revision	A								
	sheet	1								