


PCB Solder Side Cover, 3 U, 100 mm x 160 mm, 55°C

CATALOG NUMBER

61000-007



A solder side cover protects the solder side of a PCB mechanically.

CERTIFICATIONS



FEATURES

Mechanical protection of solder side

Suitable for 100 x 160 mm Euroboard

PRODUCT ATTRIBUTES

Rack Height: 3U

Package Quantity: 1

Temperature: 131°F min

Flammability Rating: UL® 94V-0

Material: Polypropylene

Product Type: Cover

Type: Solder Side Cover

ADDITIONAL PRODUCT DETAILS

The materials of the PCB cover are UL-listed. The test was conducted with material thickness 1.5 mm.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE