

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210010262

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Adapter, Form A-18mm, Internal Threads, 2 Poles with C4 Circuit, 24V, Yellow LED, A07 Series Light Adapter



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                |
|-------------------------------|--------------------------------|
| General                       |                                |
| Product Family                | Field Attachable / Accessories |
| Series                        | 121001                         |
| Form                          | A - 18mm                       |
| IP Rating                     | IP65, IP67                     |
| Material - Contact            | Brass                          |
| Overview                      | mPm DIN Valve Connectors       |
| Product Name                  | mPm                            |
| Type                          | Field Attachable Connector     |
| UPC                           | 883906499846                   |
| Physical                      |                                |
| Cable Diameter                | N/A                            |
| Coupling Type                 | Internal Thread                |
| Diagnostics / LEDs            | Yes                            |
| Diagnostics Port              | No                             |
| Gender                        | N/A                            |
| Keyway                        | None                           |
| Material - Connector Body     | Polypropylene                  |
| Material - Coupling Nut       | N/A                            |
| Material - Plating Mating     | Silver                         |
| Orientation                   | 90° Angle                      |
| Pitch - Mating Interface      | 18.00mm                        |
| Poles                         | 2                              |
| Temperature Range - Operating | -40°C to +90°C                 |
| Wire Size AWG                 | N/A                            |
| Electrical                    |                                |
| Current - Maximum per Contact | 16.0A                          |
| Voltage - Maximum             | 24V                            |
| Material Info                 |                                |
| Engineering Number            | A07C4H                         |
| Reference - Drawing Numbers   |                                |
| Sales Drawing                 | A07XXX, SD-121001-007          |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121001 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION