




Part Number : [154660450](#)
Product Description : 0.50mm Pitch Premo-Flex FFC
Jumper with Latching Ears, Same Side Contacts (Type
A), 102.00mm Cable Length, Tin (Sn) Plating, 50 Circuits
Series Number : 15466
Status : Active
Product Category : Flat-Flexible Cable (FFC)



Documents & Resources

Drawings

- [154660450 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [154660001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15466
Description	0.50mm Pitch Premo-Flex FFC Jumper with Latching Ears, Same Side Contacts (Type A), 102.00mm Cable Length, Tin (Sn) Plating, 50 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	196823195860

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Physical

Cable Length	102.00mm
Circuits (Loaded)	50
Contact Layout Type	A (same side)
Design Feature	Superior Retention
Material - Plating Mating	Tin
Net Weight	1.701/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C

Termination Style	FFC Connector
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

This document was generated on Sep 22, 2025