

Home: >

Part Number: 73396-0460

Image not available

Status: Active - Custom
Series: 73396
Category: Molex Parts

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

Go to **Part Detail**▼

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV:Not Relevant
EU RoHS:Compliant with Exemption 6(c)
EU RoHS Phthalates:Not Contained
China RoHS:
REACH SVHC:Not Contained Per - ED/01/2017 (12 January 2017)
Low-Halogen Status:Low-Halogen

Product Compliance Statement

Application Tooling **FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Active - Custom
Category	Molex Parts
Series	73396
UPC	822350667913

▼ Physical

Net Weight	3.658/g
------------	---------

▼ Solder Process Data

[Solderability Shelf Life Statement](#)

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

▼ Material Info

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
PCB Assemblies

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Literature
Press Room / Press Releases
Product Index
Sitemap

California Supply Chains Act
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

