



Representative Image

Catalog No. TC105

Description: MOUNTING PLATE AL 1X.5IN No10 SCREW

UPC No 786210822488

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Aluminum Mounting Plate, for Temperatures up to 450 Degrees Celsius (842 F), Weather and Ultraviolet Resistant, Length of 25.4mm (1.0 Inches), Width of 13.2mm (0.519 Inches), Height of 3.8mm (0.149 Inches), Screw Mounting With #10 Screw, Bulk Pack

Descriptors

Category	Cable tie mounts
Type	Aluminum Plate

Specifications

Material	Aluminum
Mounting	Epoxy Glue (TC2PA)/Screw
Operating Temperature	-60 to +250 F

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Mount Size	#10
------------	-----

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH SVHC	REACH 223 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC000449 Mounting base and -element for cable ties
Length	25.4 mm
Length	1 inch
Width	13.2 mm
Width	0.52 inch
Height	3.8 mm
Height	0.15 inch
Type of fastening	Other

ETIM	EC000449 Mounting base and -element for cable ties
Material	Metal
Material quality	Aluminium