





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
-		REVISED SPEC.	11/26/10	



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to + 85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
100 [2.54] LOCKING HEADER
SHORT BACK, STRAIGHT, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X ± .10 .XX ± .020 .XXX ± .015	ØX ØXX ØXXX	± .10 ± .015 ± .010		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS			DATE	TITLE			
DRAWN	SS	4/8/05		.100 [2.54] LOCKING HEADER SHORT BACK, STRAIGHT, PCB			
CHECKED				SIZE	PART NO.	REV.	
APPROVED				X	LHS-XX-TS	A	
REF:	S00016T	SCALE:	NTS	SHEET	1 OF 1		