



**Part Number :** [1301500212](#)  
**Product Description :** 60 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Blue  
**Series Number :** 130150  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 460R9



## Documents & Resources

**Drawings**  
[1301500212 sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130150
Description	60 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Blue
Comments	IEC Configuration 309-1/309-2
IP Rating	IP67
NEMA Configuration	N/A
Product Name	Watertite
Specialty	Pin and Sleeve
Type	Receptacle
UPC	78678872694

### Agency

UL	E145923
----	---------

### Electrical

Current - Maximum per Contact	60.0A
GFCI	No
Voltage - Maximum	250V

### Physical

Cord Type	N/A
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	241.30mm (9.500")
Lighted Connector	No

Locking Blade	No
Poles	3-pole/4-wire
Receptacle Type	Single

---

This document was generated on Sep 25, 2025