



Part Number : [190720057](#)

Product Description : VibraKrimp Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 6 (M3.5), Length 19.18mm

Series Number : 19072

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : BB-423-06

Documents & Resources

Drawings

[Drawing 190720057_sd.pdf](#)

3D Models and Design Files

[3D Model 190720057_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19072
Description	VibraKrimp Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 6 (M3.5), Length 19.18mm
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	VibraKrimp
Type	Ring
UPC	800753074033

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.778/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	6 (M3.5)
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Crimp Hand Tool	<u>640016800</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640056800</u>

This document was generated on Jul 28, 2024