


RoHS
Compliant

VERSION	DESCRIPTION	DATE
1.0	New DRAWING	2018/3/29



PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
911M-2-1-00100	671-442-A	1000±100	Orange
911M-2-1-00200	671-442-B	2000±100	Orange
911M-2-1-00300	671-442-C	3000±100	Orange
911M-2-1-00500	671-442-D	5000±100	Orange
911M-2-1-00700	671-442-E	7000±100	Orange
911M-2-1-01000	671-442-F	10000±100	Orange
911M-2-1-01500	671-442-G	15000±100	Orange
911M-2-1-02000	671-442-H	20000±100	Orange
911M-2-1-02500	671-442-I	25000±100	Orange

NOTES:

Insertion loss < 0.3 dB

6	
5	
4	Dust Cover
3	Shrinkage Tube
2	LC MM Duplex Connector (Beige housing White boot)
1	2.0mm, Duplex, MM-62.5/125 OM1, PVC, Optical Fiber Cable(Orange)
No.	Description

CnC Tech, LLC

Industrial Cable and Connector Technology

		TITLE		Patch Cord, LC-LC, MM-62.5/125 OM1, Duplex, PVC, Orange, 2.0mm, xxm	
UNIT		P/N		above	DRAWN BY
mm		Customer P/N		911M-2-1-0XXXX	CHECK BY
unless otherwise stated Tolerances mm XXX.XX ±0.3 XX.XX ±0.2 X.XX ±0.1		SIZE A4	SCALE Free	PAGE 1/1	APPROVAL BY