



Pushing Performance
Since 1945

Han-Eco 16B-Outd-Cov-w.SL-w.cord-HTE/HSE



Part number	19 43 216 5442
Specification	Han-Eco 16B-Outd-Cov-w.SL-w.cord-HTE/HSE

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Protection cover
Description of the accessory	for hoods

Version

Size	16 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
----------------	---

Commercial data

Packaging size	1
Net weight	80 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140829657
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors