



Part Number : [747630015](#)
Product Description : QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 5dB
Series Number : 74763
Status : Obsolete
Product Category : High-Speed I/O Connectors



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	High-Speed I/O Connectors
Series	74763
Description	QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 5dB
Application	Module-to-Board
Component Type	Adapter
Product Name	QSFP Plus,QSFP+
Type	N/A
UPC	883906054298

Agency

UL	E107635
----	---------

Electrical

Current - Maximum per Contact	N/A
Shielded	No
Voltage - Maximum	3.3V

Physical

Boot Color	N/A
Circuits (Loaded)	N/A
Color - Resin	Green (Light)
Flammability	94V-0
Gender	Dual
Lock to Mating Part	No
Material - Plating Mating	Nickel
Net Weight	29.204/g
Orientation	Horizontal
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	N/A

Polarized to Mating Part	No
Termination Interface Style	Through Hole

This document was generated on Sep 22, 2025

Obsolete