ET12025000J0G

ET12025000J0G - Terminal Blocks : Pluggable plug, 7.62mm pitch, horizontal wire-inlet, 12 position



ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More
Contact our sales/technical support
Sample request

Customer drawing

Environmental Compliance Report

Specifications | Download document | Mating Half

Dimensional | General | Electrical | Mechanical | Physical | Approvals / Certifications

Dimensional	
Strip length (Wire)	10 to 11 mm
Solid wire size (AWG)	8 to 24
Solid wire size (mm2)	0.2 to 6
Stranded wire size (AWG)	8 to 24
Stranded wire size (mm2)	0.2 to 6
Pitch	7.62 mm
Screw Size	M3.5
General	
Gender	Female plug
Packaging	Box
Product Type	Screw Pluggable System
Series	ET
Number of Positions	12
Electrical	
Withstanding Voltage	1.6 kV
Current rating	32 A
Voltage rating	300 V
Mechanical	
Number of mating cycles	200
Physical	
Color (Housing)	Green
Conductor entry angle	0°
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Copper
Terminal plating	Tin
Screw material	Steel
Screw plating	Zinc
Clamp material	Brass
Clamp plating	Nickel
Connection Type	Screw connection
Temperature (Operating - range)	-40 to 115 Celcius
Torque	7 Lb-in
Approvals / Certifications	
Approvals / Certifications	cULus, TUV

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from Arrow.com.