



Part Number : [1110145000](#)
Product Description : HSAutoLink Cable Assembly,
USCAR/USB MINI-B Plug-to-MINI-B Plug, 0.50m Length,
Polarization A, A
Series Number : 111014
Status : Active
Product Category : Power and Signal Cable
Assemblies

Documents & Resources

Drawings
[1110145000 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[PS-68800-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	111014
Description	HSAutoLink Cable Assembly, USCAR/USB MINI-B Plug-to-MINI-B Plug, 0.50m Length, Polarization A, A
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Mini-B-to-Mini-B
Product Name	HSAutoLink USCAR/USB
UPC	883906510022

Physical

Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	28.867/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Round

Mates With / Use With

Mates with Part(s)

Description	Part Number
HSAutoLink Right-Angle Headers	<u>49616</u>

This document was generated on Sep 24, 2025