


HONEYWELL
PART NUMBER

41SM25-H2

PRODUCT CODE
TYC2495

REV	DOCUMENT	CHANGED BY	CHECK
2	0038112	KVS 04JUN08	ASD



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.
PR - 19992REPLACES
-

CHARACTERISTICS

OPERATING FORCE - - - - 4 OZ MAX

RELEASE FORCE - - - - - 1 OZ MIN

DIFFERENTIAL TRAVEL - - - .002 MAX

OVERTRAVEL - - - - - .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

APPROVALS

KEMA, CE

11A 250V ~ T85 1E4
5A 30 Vdc T85 1E4

UL, CSA

11A 1/4 HP 125 250 VAC
5A 30 VDCBRAND
L190

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±

THIRD ANGLE PROJECTION



DRAWN

VK

25 OCT 07

CHECK

RJ

25 OCT 07

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE

TYPE

DRAWING NAME

41SM25-H2

REV

2

SCALE

-

WEIGHT

SHEET 1 OF 1