

Data Sheet | Item Number: 248-604
Mini-WSB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Vertical marking; snap-on type; white
<https://www.wago.com/248-604>



Color: white Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	21 ... 30
Marking (number)	10
Marking direction	Vertical marking
Marking color	black
Marking type	Numbers
Marking layout	Consecutive numbers per strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V0

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	6.2 g
Fire load	0.185 MJ



Commercial data		
Product Group	2 (Terminal Block Accessories)	
PU (SPU)	5 pcs	
Packaging type	Bag	
Country of origin	DE	
GTIN	4017332133456	
Customs tariff number	49119900000	

Product Classification		
UNSPSC	55121718	
eCl@ss 10.0	27-14-11-37	
eCl@ss 9.0	27-14-11-37	
ETIM 9.0	EC000761	
ETIM 8.0	EC000761	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant,No Exemption	

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 248-604

↓

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.