

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010646

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect EMC - Electromagnetic Compatibility, Single Lever Hood, Aluminum, with 1 Lever, Top Entry, Size 3A «21x21», for S-A, S-D, and S-Q Inserts, Pg11 Thread

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Comments	IP67 with screw gasket., IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Hood
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191840031

Physical

Entry Location	Top
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Lever	Stainless Steel
Net Weight	31.550/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg11
Thread Type	(Pg)

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number 7803.6212.4

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION