

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

WZ-2RDI9-DI**WZ-2RDI9-DI**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
7

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO15200
M B F	4 FEB 66
B	CO 63526
D C S	18 JUN 88
C	CO 77589
TSM	29 MAR 94
D	CO93346
DLT	4 SEP 98

CHECK


FORMTEK

FO-50378

DRAWN

CHECK

M B F 4 FEB 66



NOTE

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — 9-13 OZ

RELEASE FORCE — — — — 4 OZ MIN

DIFFERENTIAL TRAVEL — — .0004-.0020

OVERTRAVEL — — — — .060 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C

UL LISTED — FILE E12252

CODE L88 15A-125, 250 OR 480 VAC
1/3HP-125 OR 250 VAC
1/2A-125 VDC; 1/4A-250 VDC

L288

L299

L306 16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .056 LB