



Part Number : [5017865091](#)
Product Description : 0.50mm Pitch Easy-On FFC/
FPC-to-Board Connector, Receptacle Housing
Assembly, Vertical, Surface Mount, with Grounding
Terminals, Separated Gold (Au) Plating, 50 Circuits
Series Number : 501786
Status : Active
Product Category : FFC / FPC Connectors



Documents & Resources

Drawings

[5017865091_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5017865091.dxf](#)

Specifications

[SPK-501786-001-001.pdf](#)

[PS-501786-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	501786
Description	0.50mm Pitch Easy-On FFC/FPC-to-Board Connector, Receptacle Housing Assembly, Vertical, Surface Mount, with Grounding Terminals, Separated Gold (Au) Plating, 50 Circuits
Comments	Requires a custom FFC/FPC with notches
Product Name	Easy-On
UPC	883906751302

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Flexi-Latch
Circuits (Loaded)	50

Color - Resin	Black
Contact Position	N/A
Durability (mating cycles max)	20
Mated Height	8.95mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	863.843/mg
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Premo-Flex LVDS Jumpers, 100±10 Ohms Differential Impedance	<u>15022</u>
0.50mm Pitch Premo-Flex LVDS Jumpers, 90±10 Ohms Differential Impedance	<u>15922</u>

Use with Part(s)

Description	Part Number
0.50mm Pitch FFC-to-Board Plug Jacket, 50 Circuits	<u>5031505009</u>
0.50mm Pitch FFC-to-Board Plug	<u>5031515009</u>

Jacket Cover, 50 Circuits	
0.50mm Pitch FFC-to-Board Plug Jacket, 50 Circuits	<u>5017835009</u>

This document was generated on Sep 22, 2025