



Part Number : [1300230004](#)
Product Description : Super-Safeway Single Button,
3 Pin, Single-Pole, Single-Throw, Normally Open, 10A,
Snap Action Switch, Nitrile/PVC Switch Boot, 125/250V
AC, Mini-Change Connection
Series Number : 130128
Status : Active
Product Category : Push Button Products
Engineering Part Number : 55504



Documents and Resources

Drawings

[1300230004_sd.pdf](#)

Specifications

[1300230001_APPSPEC-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Push Button Products
Series	130128
Description	Super-Safeway Single Button, 3 Pin, Single-Pole, Single-Throw, Normally Open, 10A, Snap Action Switch, Nitrile/PVC Switch Boot, 125/250V AC, Mini-Change Connection
Enclosure Rating	Weather Resistant
Product Name	Super-Safeway
Type	Enabling Switch, PushButton Pendant Station
UPC	78678855509

Agency

UL	E70531
----	--------

Electrical

Voltage - Maximum	125V AC / 250V AC
-------------------	-------------------

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Cord Type	N/A
Emergency Stop	No

Material - Body	Nylon
Net Weight	70.760/g
Number of Speeds	Single
Packaging Type	Carton
Poles	1

This document was generated on May 19, 2026