





| Rev | AWO # | Description | Date     | Appr |
|-----|-------|-------------|----------|------|
| -   |       | RELEASED    | 12/08/10 |      |

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



# SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-2  
Insulator color: White  
Contacts: Brass  
Plating: Tin over Copper underplate overall  
Electrical:  
Operating voltage: 250V AC,DC  
Current rating: 7A AC,DC  
Contact resistance: 10 mohms max  
Insulation resistance: 1,000 Mohms min  
Dielectric withstanding voltage: 1,500 VAC for 1 minute  
Temperature Rating:  
Operating temperature: -25°C to +85°C  
Environmental:  
Lead free, RoHS compliant

Positions: 2 thru 10  
A = .200 [5.08] x No. of Positions  
B = .200 [5.08] x No. of Spaces

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

.200 [5.08] POWER HEADER, STRAIGHT

| UNLESS OTHERWISE SPECIFIED<br>ALL DIMENSIONS ARE INCHES [MM] |              |          |  |
|--------------------------------------------------------------|--------------|----------|--|
| TOLERANCES: EXCEPT AS NOTED                                  |              |          |  |
| INCHES                                                       | HOLES        |          |  |
| .X ± .10                                                     | ØXX ± .10    |          |  |
| .XX ± .020                                                   | ØXXX ± .015  |          |  |
| .XXX ± .015                                                  | ØXXXX ± .010 |          |  |
| APPROVALS                                                    | DATE         |          |  |
| DRAWN                                                        | DY           | 12/08/10 |  |
| CHECKED                                                      |              |          |  |
| APPROVED                                                     |              |          |  |

| TITLE                              |  | PART NO.   |  | REV.         |  |
|------------------------------------|--|------------|--|--------------|--|
| .200 [5.08] POWER HEADER, STRAIGHT |  | LHF-XX-SA2 |  | -            |  |
| REF: S00099T                       |  | SCALE: NTS |  | SHEET 1 OF 1 |  |