

Representative Image

Catalog No. CI08-90-DT2

Description: 2WAY DEUTSCH CONNINTERFACE 90 NC08

UPC No 5020963024092

Home > Cable Protection Systems > Harnessflex > Electrical connector assembly

Hinged Connector Interface Fitting, 90 Degree Elbow with 360 Degree Swivel, 2-Way Deutsch DT Connector to Conduit, Conduit Size NC08/NW7.5, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

Descriptors

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

Specifications

Connection	90 degree elbow, 360 degree swivel, 2-way connection
Material	Polyamide/Nylon
Color	Black
Insulation	IP40
Temperature Rating	-40 to 120 C
Environmental Conditions	Very High UV Protection

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant

Dimensions

Size	Conduit Size NC08/NW7.5

Compliance and Certifications

RoHS	RoHS3 Compliant

by ABB

Downloaded from Arrow.com.