Pushing Performance
Since 1945

MPP-PFT-ix-wo_insert



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 2514
Specification	MPP-PFT-ix-wo_insert
HARTING eCatalogue	https://harting.com/97000002514

Identification

Category	Connectors
Series	HARTING Mini PushPull
Identification	HARTING ix Industrial®
Element	Panel feed trough set
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	PushPull
Pack contents	Flange gasket Board drillings for M2.5

Technical characteristics

Limiting temperature	-40 ... +70 °C
Storage temperature	-60 ... +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (hood/housing)	Polybutylene terephthalate (PBT)
Colour (hood/housing)	Black
Material (seal)	PTS
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124

Commercial data

Packaging size	10
Net weight	3.5 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440114 Rectangular connector (for field assembly)

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.