



Part Number : [734200391](#)
Series Number : 73420
Status : Active - Proprietary
Product Category : RF / Coaxial Connectors




Drawings

[734200391 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active - Proprietary
Category	RF / Coaxial Connectors
Series	73420
Description	SMP-MAX Plug, Straight, Smooth Bore, Catchers Mitt, Panel Mount, Press-in, Gold (Au) Plated Body, Tray, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	SMP-MAX
Style	Panel
Type	Subminiature
UPC	884982584266

Electrical

Frequency	10 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 330 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Plug
Keying to Mating Part	N/A
Net Weight	2.226/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Press-In
PCB Mounting	N/A
Reverse Polar	No

Wire/Cable Type	N/A
-----------------	-----

Solder Process Data

Lead-Free Process Capability	N/A
Max-Cycle	2
Max-Temp	260

This document was generated on Sep 17, 2025