



Part Number : [190750017](#)
Product Description : InsulKrimp Star Ring Tongue
Terminal for 16-14 AWG Wire, Stud Size 10 (M5),
Carton
Series Number : 19075
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : SRB-229-10X



Documents and Resources

Drawings

[190750017 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19075
Description	InsulKrimp Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal
UPC	800753079694

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC

Material - Plating Mating	Tin
Net Weight	0.679/g
Packaging Type	Carton
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	4.45mm
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640011900</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640051900</u>

This document was generated on May 21, 2026