



Part Number : [1300088058](#)

Product Description : Mini-Change C-Size Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length

Series Number : 130008

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 302100B80M050



Documents and Resources

Drawings

[1300088058_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length
IP Rating	IP68
Product Name	Mini-Change
Type	Single Ended
UPC	887191920849

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	600V

Physical

Cable Diameter	8.50mm (.335")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None

Material - Cable Jacket	TPU
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Alloy
Material - Plating Mating	Gold
Net Weight	571.000/g
Orientation	Straight to Pigtail
Poles	12
Temperature Range - Operating	-4° to +105°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	19, 22

This document was generated on Dec 26, 2025