TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

MAGNET WIRE TERMINALS



✔ Active

TE CONNECTIVITY (TE)

MAG-MATE CONTACT.187 WITH SOLDER PIN

Magnet Wire Terminals & Splices | MAG-MATE

1534681-1
TE Internal Number: 1534681-1

EU RoHS Compliant
EU ELV Compliant

Terminal Type Solder Post
Magnet Wire Size (mm) .265 – .335
Magnet Wire Size (AWG) 30 – 26
Material Thickness (in) .0126
Packaging Method Reel, Reel/Carton

3D PDF

DOCUMENTATION

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Downloaded from Arrow.com.

Catalog Pages/Data Sheets

Magnet Wire Terminals & Splices

PDF

English

CAVITY FOR MAG-MATE CONTACT WITH SOLDER PIN

PDF

English

Product Specifications

Product Specification

MAG-MATE Standard Series 187 And 300 Terminals

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Contact Features

Terminal Type Solder Post

Dimensions

Magnet Wire Size (mm) .265 – .335
Magnet Wire Size (AWG) 30 – 26
Material Thickness (in) .0126

Packaging Features

Packaging Method Reel, Reel/Carton

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.