

C504F Scalable Clip 1.0 mm

Part No. C504 10M006 118 3

- All-purpose (e.g. antenna or grounding contact)
- For flat contact area
- Same Pad-Layout for all scalable Clips
- SMT solderable
- Tape & Reel packaging
- Pick & Place capable



View represents all available contact positions.

For more information, please contact us [here](#).

Series Mobile Connectors
Subseries Mobile Connectors C504F

COMMON CHARACTERISTICS		
No. of contacts		1
Termination		solder
Total height (undeflected)		1.0 mm
Stroke		0.4 mm
CLIMATICAL CHARACTERISTICS		
Operating temperature		-40 °C...+85 °C
MECHANICAL CHARACTERISTICS		
Mechanical lifetime		100 mating cycles
Contact force		Min. 0.2 N
MATERIALS		
Contacts		Stainless steel
Plating contacts		min. 0.5 µm Au
Plating solder area		min. 0.025 µm Au
Underlayer		min. 1,27 µm Ni.

