



Pushing Performance
Since 1945

HIGH STR. FO CABLE-MM-2CH.-100M,RING




Image is for illustration purposes only. Please refer to product description.

Part number	33 58 751 1000 001
Specification	HIGH STR. FO CABLE-MM-2CH.-100M,RING
HARTING eCatalogue	https://harting.com/33587511000001

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	FO cable
Description of the cable	Multimode

Version

Cable length	100 m
Core structure	62.5 / 125 µm

Technical characteristics

Cable diameter	7 mm
----------------	------

Material properties

Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	5,000 g
Net weight	36 g/m
Country of origin	Germany
European customs tariff number	85447000
GTIN	5713140273917
eCl@ss	27061803 Fiber optic cable
ETIM	EC000034
UNSPSC 24.0	26121607