


**Part Number :** [525594033](#)

**Product Description :** Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 40 Circuits, Tin-Silver-Bismuth Plating

**Series Number :** 52559

**Status :** Obsolete

**Product Category :** FFC / FPC Connectors



---

## Documents and Resources

[525594033 stp.zip](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications


[525590003-A00.pdf](#)

[PS-52559-019-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Obsolete   |
| Category     | FFC / FPC Connectors   |
| Series       | Slider   |
| Description  | Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 40 Circuits, Tin-Silver-Bismuth Plating |
| Product Name | Easy-On  |
| UPC          | 887191289908   |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum             | 50V  |

### Physical

|                                |         |
|--------------------------------|---------|
| Actuator Type                  | Slider  |
| Circuits (Loaded)              | 40      |
| Color - Resin                  | Natural |
| Contact Position               | N/A     |
| Durability (mating cycles max) | 20      |
| Flammability                   | 94V-0   |
| Mated Height                   | 3.90mm  |

|                                |                       |
|--------------------------------|-----------------------|
| Material - Metal               | Phosphor Bronze       |
| Material - Plating Mating      | Tin-Silver-Bismuth    |
| Material - Plating Termination | Tin-Silver-Bismuth    |
| Material - Resin               | Nylon                 |
| Net Weight                     | 471.542/mg            |
| Orientation                    | Vertical              |
| Packaging Type                 | Embossed Tape on Reel |
| PCB Locator                    | No                    |
| PCB Mounting                   | Surface Mount         |
| PCB Retention                  | Yes                   |
| PC Tail Length                 | 2.00mm                |
| Pitch - Mating Interface       | 0.50mm                |
| Pitch - Termination Interface  | 0.50mm                |
| Polarized to PCB               | No                    |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40° to +85°C         |
| Wire/Cable Type                | FFC/FPC               |

---

## Mates With / Use With

### Mates with Part(s)

| Description                         | Part Number  |
|-------------------------------------|--------------|
| 0.50mm Pitch Premo-Flex FFC Jumpers | <u>15166</u> |
| 0.50mm Pitch Premo-Flex FFC Jumpers | <u>15266</u> |
| 0.50mm Pitch Premo-Flex FFC Jumpers | <u>15366</u> |
| 0.50mm Pitch Premo-Flex FFC Jumpers | <u>98266</u> |

---

This document was generated on Jun 05, 2026