

**Part Number :** [22011032](#)

**Product Description :** 2.50mm Pitch KK Wire-to-Board Housing, Female, Friction Lock, for 2759/5159 Crimp Terminals, 3 Circuits

**Series Number :** 5051

**Status :** Not Recommended For New Design

**Product Category :** Connector Housings

**Engineering Part Number :** 5051-03

---

## Documents and Resources

### Drawings

[022011032\\_sd.pdf](#)

[022011032\\_stp.zip](#)

### Specifications

[SPK-5051-001-001.pdf](#)

[PS-5045-001-001.pdf](#)

[PS-5045-002-001.pdf](#)

[PS-5045-003-001.pdf](#)

[PS-5045-004-001.pdf](#)

[50510000-000.pdf](#)

[50510002-PS-000.pdf](#)

[PS-5051-005-001.pdf](#)


[PS-5051-006-001.pdf](#)

[PS-5102-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Not Recommended For New Design
Category	Connector Housings
Series	5051
Description	2.50mm Pitch KK Wire-to-Board Housing, Female, Friction Lock, for 2759/5159 Crimp Terminals, 3 Circuits
Application	Wire-to-Board
Product Name	KK
UPC	800753594340

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	3
--------------------	---

Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	433.800/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini-Latch / KK Single Row Vertical Headers	<u>5045</u>
Mini-Latch / KK Single Row Right-Angle Headers	<u>5046</u>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black	<u>797580007</u>
Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black	<u>797580015</u>
KK 254 Female Crimp Terminals	<u>2759</u>
KK Cat Ear Female Crimp Terminals	<u>5159</u>

---

This document was generated on May 27, 2026