Part Number : 1301460074
Product Description : Watertite Extreme Receptacle Connector, 2 Pole/3 Wire, NEMA 6-15, 250V, Cord Grip Body Size F2, Silicone Husk
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 15W49



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle Connector, 2 Pole/3 Wire, NEMA 6-15, 250V, Cord Grip Body Size F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA 6-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871103

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire

Downloaded from Arrow.com.

Receptacle Type	Single

Downloaded from Arrow.com.