

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0981721001

Status:

Active - Custom

Description:

5.00mm (.197") NSCC Wire-to-Wire 2.80mm (.110") Receptacle Housing, with TPA™, 6 Circuits, Natural

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	98172
Application	Power
Product Name	NSCC
Physical	
Circuits (maximum)	6
Color - Resin	Black, Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm (.197")
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	18A
Material Info	
Country of Origin	BR, CN, DE, SK
Reference - Drawing Numbers	
Application Specification	RAS-98172-001
Packaging Specification	PP-98172



Series
image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

98172Series

Mates With

Harnessmaker specific

Use With

2.80mm (.110") UCC terminals (98898-series)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION