



**Part Number :** [1300250413](#)

**Product Description :** Mini-Change A-Size Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 18/15 AWG, Gray DeviceNet Thick Flex-Rated Cable, 4.0m (13.12') Length

**Series Number :** 130025

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** DNF11A-M040

---

## Documents and Resources


### Drawings

[1300250413\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130025
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 18/15 AWG, Gray DeviceNet Thick Flex-Rated Cable, 4.0m (13.12') Length
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Double Ended
UPC	78678849734

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

### Physical

Cable Diameter	12.10mm (.480")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change

Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	357.230/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thick Flex-Rated Cable
Wire Size (AWG)	15, 18

---

This document was generated on May 23, 2026