



**Part Number :** 1300940263

**Product Description :** Standard Duty Support Grip, Offset Eye, Closed Mesh, Single Weave, Cable  
Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1197.48kg (2640 lbs)



**Series Number :** 130094

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 35066

---

## Documents & Resources

### Drawings

[PK-130227-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

### **Part Details**

#### **General**

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Offset Eye, Closed Mesh, Single Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1197.48kg (2640 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835066

#### **Agency**

CSA	LR32159
-----	---------

#### **Physical**

Approximate Break Strength	1197.48kg (2640 lbs)
Bale Length	0.152m (6.00")
Body Style	Straight
Cable Diameter	44.45-50.55mm (1.750-1.990")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.508m (20.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

---

This document was generated on Sep 18, 2025