



PCB layout

Specifications:

Current Rating: 1.5A AC/DC

Voltage Rating: 30V AC/DC

Contact Resistance: 20m Ohm. Max.

Insulation Resistance:1000M Ohm. Min.

Withstanding Voltage: 750V AC/Minute

Operating Temperature Range:-40°C ~ +105°C

Materials:

Insulator:LCP(UL94V-0)

Insulator Color:White

Contact: Brass

Plating:30u" Gold Plated on Contact Area,
Tin Plated on Solder Tails.

△ Shell:Brass,Nickel Plated

RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X=±0.20

.XX=±0.15

CHECKED:


UNIT: MM

SCALE:1:1

APPROVAL:

SHEET: 1 / 2

PROJECTION:



CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

USB A Male SMD Type,30u"

PART NO:

1002-016-01101-TR

SIZE




A4

REV

DATE




FILE

BY



Note:

- 1.Material : Black Conductive Polystyrene Alloy
100% recyclable.
- 2.Thickness : 0.35 ± 0.05 mm
- 3.Component load per 13" reel :500 Pcs.
- 4.Carton Size:350*350*296(mm)



Pin No	W	PCS/R	R/CTN	Q'TY
04	44	500	5	2500

RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X= ± 0.20

.XX= ± 0.15

CHECKED:


UNIT: MM

SCALE:1:1

APPROVAL:

SHEET: 2 / 2

PROJECTION:



CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

USB A Male SMD Type,30u"

PART NO:

1002-016-01101-TR

SIZE

A4

REV

DATE

FILE

BY