


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER		MATERIAL		MARKER SIZE inches [mm]		LABELS PER SHEET		SHEET QTY.		STANDARD PKG. QTY.		2				
S100X650YAJ		GMY6 CLEAR POLYESTER FILM		1.000 [25.4] X X 6.500 [165.1]		7		143		1000						
													CAD FILENAME/LAYERS I00472CH_DC_C10208/02C			
													PANDUIT CORP. TINLEY PARK, ILLINOIS			
													CUSTOMER DRAWING OPTIMUMM SELF-LAM. LASER INKJET PRINTABLE LABELS			
2	10/29/09	RVU		UPDATE ON TOLERANCES. ADD +/- .062.					5898	R			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ± 2	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
1	8/12/08	RVU		CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.					5516	R						
0	6-29-06	RVU		DRAWING RELEASE. MAT'L WAS GMY2.					4568	R			DRAWN BY RVU	SEE TABLE	SCALE	
A	9-22-04	RVU		ENGRG. RELEASE.					0000	R			DATE 9/22/04		DRAWING NO. C10208	DWG SIZE A
REV	DATE	BY	CHK	DESCRIPTION					ECN - R	CUST	SUP		CHK'D			