


	1	2	3	4	5	6	7	
A	RoHS compliant							A
B								B
C								C
D								D
E								E
F								F
G								G
H								H
	1	2	3	4	5	6	7	

RoHS compliant



Notes
 Material:SR25
 Dielectric strength: 380kV/cm
 Heat resistance:215°C
 Tensile strength: 80N/mm

Scale	1:1					Date	Name	Customer-No.
TOLERANCE					Drawn	20.08.2009	Dean	
X.	±X				Approved	10.03.2010	Andy	
X.X	±X							
X.XX	±X							
DIM	TOL	②	Modify drawing layout	10.03.2010	Andy		Drawing-No.	
X.°	±X°	①	Drawn	20.08.2009	Dean		ASS 0489A HS	rev02
X.X°	±X°						Replace	Sheet
Angle	TOL	Id.	Modification	Date	Name			