

Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

M Series

>

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



MSAS-08BFFB-SL7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

-

1

+

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

M Series....
CAP-WBDF SMA1
-40°C ~ +105°C

- 0 +

M Series....
CAP-WBDF SMA2
-40°C ~ +105°C

- 0 +

M Series....
CAP-WBDF SPB1
-40°C ~ +105°C

- 0 +

M Series....
IA-A08M-A08M-...
-20°C ~ +85°C

- 0 +

M Series, M12, A...
M12A-08PMMP-...
-40°C ~ +105°C

- 0 +

M Series, M12, A...
M12A-08PMMP-...
-40°C ~ +105°C

- 0 +

Add to Cart

Inquiry

Specifications		Download / CAD	
Nominal Current		Connector Type	
2A		Field Installable	
Shielded		No. of Contacts	
Metal, Shielded		08	
Connector Gender		Backshell	
Female		Straight	
Mating Style		IP Rating	
Screw Thread		IP67	
Assembly Style			
Screw-in			
<div><div></div>More Options</div>			

People Also Bought

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Downloaded from [Arrow.com](#)