



By Burndy
Catalog # BIBS2503

Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 1 Sided Entry, 10 AWG-250 kcmil, Al/Cu Rated

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - UL Listed Direct Burial	No
Buy American Compliant	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2024);TAA Compliant (All status valid till December 2024)

Conductor

Conductor - Copper Str Size Range	10 AWG - 250 kcmil
Conductor Type	AL C Str-Size;CU C Str-Size
Conductor - AL Str Size Range	10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	3
Number Of Ports	3

Current

Voltage - Maximum	600 V
Operating Voltage	600 V

Dimensions

Dimension - Width inch	2.07 in
Dimension - Width mm	53 mm
Dimension - Height inch	2.13 in
Dimension - Height mm	54 mm

General

Sub Brand	UNITAP
Physical Attribute - Screw Type	Allen
Insulation Type	Plastisol
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC 12 Digit	781810223994
UPC 14 Digit GTIN	00781810223994
Material	Aluminum
Hex Key	5/16
UPC	781810223994

Logistics

Carton Quantity	24
Minimum Pack Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)

